
Superior Amenities -




Model # T46RCPEDPOR-3ADA




3/25/2020 Page 1 of 10

HARDWARE








7/16" Washer



7/16" Hex Nut











5/16" Kep Nut



3/8" x 1" Carriage Bolt



3/8" Washer





3/8" Hex Nut





3/25/2020 Page 2 of 10

TOOLS REQUIRED











3/25/2020 Page 3 of 10

PRODUCT SPECIFICATIONS

T46RCPEDPOR-3ADA 46" ACCESSIBLE PORTABLE TABLE WITH 3 SEATS

Top & Seats: 2" x 2" x 1/8" angle frame. 3/4" #9 steel expanded metal. 7 gauge x 1-1/2" flat bar center support and mounting bracket understructure. Top is additionally supported to the corners with 7 gauge x 1-1/2" flat bar. Electrically MIG welded.

Coating: Oven fused functionalized polyethylene copolymer-based thermoplastic. Fluidized bed coating application with superior mechanical performance, impact resistance and UV-stability.

Frame: 3" square pre-galvanized structural steel tubing. Brace attachment points are 1-1/2"x2"x3/16" steel flat bar. Top is attached with 7 gauge 2"x2" die formed angle. Seat mounting points are 7 gauge x 1-1/2" die stamped steel flat bar. All electrically MIG welded.

Frame Coating: Electrostatic powder coated application oven cured.


Hardware: All stainless steel hardware fasteners.

Dimensions: Top is 46" x 55" x 31-5/16" high. Seats are 10" wide x 36" long x 17-5/8" high. Outside to outside dimensions of 3 seat table is 69-7/8" x 75-3/4".



3/25/2020 Page 4 of 10


COMPONENTS



| ITEM NO. | PartNo | DESCRIPTION | Qty. |
|----------|--------------|---|------|
| 1 | 01-04-0683 | 338 PEDPOR post | 1 |
| 2 | P-01-04-0150 | H Bracket | 1 |
| 3 | 01-04-0684 | 338 ped por arm | 3 |
| 4 | RC36-S | 3' long x 10" wide regal expanded seat | 3 |
| 5 | RC46H-T | 46" x 57" ADA square regal expanded top | 1 |
| 6 | 33-05-0029 | 5/16" x 1" Machine Bolt (SS) | 16 |
| 7 | 33-02-0007 | 5/16" SS Washer | 32 |
| 8 | 33-03-0012 | 5/16" Kep Nut (SS) | 16 |
| 9 | 33-06-0050 | 7/16" x 5-1/2" Machine Bolt | 8 |
| 10 | 33-02-0004 | 7/16" SS Washer | 16 |
| 11 | 33-01-0006 | 7/16" Hex Nut (Zinc) | 8 |
| 12 | 33-06-0042 | 3/8" x 1" Carriage Bolt (SS) | 4 |
| 13 | 33-02-0008 | 3/8" Flat Washer (SS) | 4 |
| 14 | 33-01-0018 | 3/8" Hex Nut (SS) | 4 |
| 15 | HWM0490 | Cap Square Ribbed Tube Ins 3" Tube od(10- 14ga)black | 3 |




3/25/2020 Page 5 of 10



Attach the Arms to the Post using specified hardware.




3/25/2020 Page 6 of 10



Attach the H-Bracket to the Post using specified hardware.




3/25/2020 Page 7 of 10



Attach the 46" Square Top to the H-Bracket using specified hardware.




3/25/2020 Page 8 of 10



Attach the Seats to the Arms as shown using specified hardware.



3/25/2020 Page 9 of 10



3/25/2020 Page 10 of 10